

Fluke 945 Sound Meter



Key features

- Max/Min
- Frequency weighting ranges: A, C
- Auto power off
- Auto ranging
- Backlit display

Product overview: Fluke 945 Sound Meter

The Fluke 945 Sound Level Meter has been designed to meet the measurement requirements of safety Engineers, Health, Industrial safety offices and quality control in a wide variety of industrial environments. It offers two types of measurements: A weighting and C weighting. The A weighting is for general noise sound level and the C weighting is for measuring sound level of acoustic material control in various environments. The Fluke 945 conforms to the IEC651 Type 2, ANSI S1.4 Type 2, and JISC1502 requirements for Sound Level Meters.

Applications:

- Environmental Health and Safety testing and verification
- Sound testing for education environments
- Heavy and light industry sound testing
- Healthcare environment testing
- Safety testing

Specifications: Fluke 945 Sound Meter

Fluke 945			
Measurement parameter	Range	Resolution	Accuracy
Measurement of environment noise (A weighted)	30 to 130 dB	0.1 dB	±1.5 dB (ref 94dB@1KHZ)
Measurement of mechanical noise (C weighted)	35 to 130 dB	0.1 dB	±1.5 dB (ref 94dB@1KHZ)

Specifications	
Display	0.1 dB steps on 4-digit LCD screen
Frequency response	From 31.5 Hz to 8 kHz
Safety standard	CE, designed to meet IEC651 Type2, ANSI S1.4 Type 2
Microphone	0.5-inch electric condenser microphone
Time weighting	Fast slow
Dimensions	200 x 56 32 mm
Warranty	1 year

Ordering information



Fluke 945

Fluke 945 Sound Level Meter

- Carrying case
- 9V battery
- User manual



Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2021 Fluke Corporation.
Specifications subject to change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**