

Fluke BC430 Line Voltage Adapter/Battery Charger



Key features

- Mains (Line Voltage): switchable 115 V \pm 15% or 230 V \pm 15%
- Equipped with a male receptacle plug that must be connected to a line cord/adapter appropriate for local use. (Line cord/adapter not included)

Product overview: Fluke BC430 Line Voltage Adapter/Battery Charger

Provides power cord operation and charging for Fluke 430 Series Power Quality Analyzers.

Specifications: Fluke BC430 Line Voltage Adapter/Battery Charger

Specifications	
Frequency (all versions)	50...60 Hz \pm 10%
Output voltage	17.8 V DC
Output power	15 W
Power consumption	23.7 VA
Max. voltage to ground	600 V CAT IV per IEC 1010-1

Ordering information



Fluke BC430

BC430 Line Voltage Adapter/Battery Charger

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa +31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500

Fluke Electronics (Malaysia) Sdn Bhd
Suite D-3A-4, Block D
SouthGage Commercial Centre, No2
Jalan Dua Off Jln Chan Sow Lin
55200 KL
Malaysia
Email: info.asean@fluke.com
www.fluke.com/my

©2021 Fluke Corporation. Specifications subject to
change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**