

TECHNICAL DATA

# Fluke PV350 Pressure Vacuum Module



## Key features

- Compatible with all Fluke and most popular DMMs
- Digital pressure and vacuum measurements in a single module
- Transducer sealed in 316 stainless steel compatible with variety of liquids and gases
- Measures vacuum to 76 cm Hg
- Displays results in English (psig of Hg) or metric (kPa or cm Hg) units
- Measures pressure to 3447 kPa (500 psig)
- One year warranty

# Ordering information



**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Europe/M-East/Africa +31 (0)40 267 5100  
In Canada (800)-36-FLUKE  
From other countries +1 (425) 446-5500

**Fluke Electronics (Malaysia) Sdn Bhd**  
Suite D-3A-4, Block D  
SouthGage Commercial Centre, No2  
Jalan Dua Off Jln Chan Sow Lin  
55200 KL  
Malaysia  
Email: info.asean@fluke.com  
www.fluke.com/my

©2021 Fluke Corporation. Specifications subject to  
change without notice.  
12/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**