

Fluke BP7235 NiMH Battery Pack



Key features

7.2V 3500 mA-hour rechargeable Ni-MH battery pack. This item replaces BP7217 Ni-Cd Battery Pack

Includes one battery pack.

Product overview: Fluke BP7235 NiMH Battery Pack

7.2 V 3500 mA-hour rechargeable Ni-MH battery pack. Provides typical 16-hour battery life when used in 700 or 740 Calibrator.

Specifications: Fluke BP7235 NiMH Battery Pack

| General Specifications | |
|------------------------|---|
| Material | Six 1.2 V DC Ni-MH cells in custom-molded ABS/PC-blend case |
| Application | 7.1 x 2.2 x .9 in (150 x 56 x 22 mm) |
| Dimensions | 7.1 x 2.2 x .9 in (150 x 56 x 22 mm) |
| Weight | 11 oz / 310g |
| Warranty | One year |

This item replaces BP7217 Ni-Cd Battery Pack.

Ordering information



Fluke BP7235

NiMH Battery Pack

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa +31 (0)40 267 5100

In Canada (800)-36-FLUKE

From other countries +1 (425) 446-5500

Fluke Electronics (Malaysia) Sdn Bhd

Suite D-3A-4, Block D

SouthGage Commercial Centre, No2

Jalan Dua Off Jln Chan Sow Lin

55200 KL

Malaysia

Email: info.asean@fluke.com

www.fluke.com/my

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

Modification of this document is not permitted without written permission from Fluke Corporation.