

TECHNICAL DATA

Fluke CXT280 Extreme Case



Key features

- Dimensions: 27.9 by 31.8 by 12.7 cm (11 by 12.5 by 5-Inch)
- Buoyancy allows case to float in salt water with 3.6 kg (7.94 lb) load
- Includes an automatic purge valve for quick equalization after changes in atmospheric pressure
- Features an exclusive 6.4 mm (0.25 in) neoprene O-ring and ABS latches for excellent seal

Product overview: Fluke CXT280 Extreme Case

Unbreakable, watertight, airtight, dustproof, chemical resistant and corrosion proof case.

Ordering information



Fluke-CXT280

Fluke CXT280 Extreme Case

For use with the following test tools:

- Multimeters: 287, 289
- Earth Ground Testers: 1621

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa +31 (0)40 267 5100

In Canada (800)-36-FLUKE

From other countries +1 (425) 446-5500

Fluke Electronics (Malaysia) Sdn Bhd

Suite D-3A-4, Block D

SouthGage Commercial Centre, No2

Jalan Dua Off Jln Chan Sow Lin

55200 KL

Malaysia

Email: info.asean@fluke.com

www.fluke.com/my

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

Modification of this document is not permitted without written permission from Fluke Corporation.