

Fluke EI-1623 Selective/Stakeless Clamp Set



Product overview: Fluke EI-1623 Selective/Stakeless Clamp Set

The Selective/Stakeless clamp set is used along with the Fluke 1623-2 and 1625-2 to perform Selective and Stakeless testing. Selective testing means using one clamp along with earth ground stakes to provide earth ground loop resistance values for one earth ground electrode. Stakeless testing uses both clamps provided to perform earth ground loop resistance measurement without stakes. Both tests have the advantage of providing measurements with no disconnection from the grounding system! Safer and quicker. Already included in the Fluke 1623-2 and 1625-2 kits. Both clamps have a 50.8 mm (2-inch) inner diameter.

Ordering information



Fluke EI-1623

Fluke EI-1623 Selective/Stakeless Clamp Set

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa +31 (0)40 267 5100

In Canada (800)-36-FLUKE

From other countries +1 (425) 446-5500

Fluke Electronics (Malaysia) Sdn Bhd

Suite D-3A-4, Block D

SouthGage Commercial Centre, No2

Jalan Dua Off Jln Chan Sow Lin

55200 KL

Malaysia

Email: info.asean@fluke.com

www.fluke.com/my

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

Modification of this document is not permitted without written permission from Fluke Corporation.