

TECHNICAL DATA

Fluke i17XX-flex3000 iFlex® Current Clamp



Product overview: Fluke i17XX-flex3000 iFlex® Current Clamp

The Fluke 17XX 24 inch iFlex® flexible current probes expand the measurement range of the Fluke 17XX Energy or Power Logger to 3000A AC while providing the ultimate measurement flexibility. The iFlex® probes connect directly to the logger, displaying current measurements without error prone scaling factors. The 1.8 m (6 ft) cord allows separation between the measurement location and the logger making it easier to view the display. Fluke 17XX iFlex® cables are available in 12, 24, and 36 inch.

Ordering information



i17XX-flex3000

3000A 24 inch iFlex® Current Clamps

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa +31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500

Fluke Electronics (Malaysia) Sdn Bhd
Suite D-3A-4, Block D
SouthGage Commercial Centre, No2
Jalan Dua Off Jln Chan Sow Lin
55200 KL
Malaysia
Email: info.asean@fluke.com
www.fluke.com/my
©2021 Fluke Corporation. Specifications subject to
change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**