


TECHNICAL DATA

## Fluke MBX 300 Poleset Mounting Kit



### Product overview: Fluke MBX 300 Poleset Mounting Kit

Built with all-weather IP65 enclosures, the Fluke 1743 and 1744 Power Quality Loggers are ready to be installed wherever the job demands. With the durable mounting kit, the Fluke 1743 and 1744 can be easily and safely secured to utility poles or suspended from other hardware. The package includes a mounting plate and strap that affix with existing fasteners and attachment points on the loggers.

## Ordering information



---

**Fluke 1743/44 Poleset**

Fluke MBX 300 Poleset Mounting Kit

---

**Fluke MBX Clamp 1A/10A**

Fluke Set of 3 1A/10A Current Clamps

---

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**

PO Box 9090, Everett, WA 98206 U.S.A.

**Fluke Electronics (Malaysia) Sdn Bhd**

Suite D-3A-4, Block D  
SouthGage Commercial Centre, No2  
Jalan Dua Off Jln Chan Sow Lin  
55200 KL  
Malaysia

Email: [info.asean@fluke.com](mailto:info.asean@fluke.com)

[www.fluke.com/my](http://www.fluke.com/my)

©2021 Fluke Corporation. Specifications subject to  
change without notice.  
12/2021

**For more information call:**

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa +31 (0)40 267 5100

In Canada (800)-36-FLUKE

From other countries +1 (425) 446-5500

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**