

TECHNICAL DATA

Fluke 80K-40 High Voltage Probe



Key features

- A high voltage probe that allows a multimeter to measure up to 40,000V respectively. Intended for low energy applications only
- One year warranty

Product overview: Fluke 80K-40 High Voltage Probe

The 80K-40 is a high voltage probe designed to extend the voltage measuring capability of an AC/DC voltmeter to 40,000 volts peak AC or DC Overvoltage Category I. This means the probe can only be used to make measurements on energy limited circuits within equipment. Examples include high voltage within televisions or photo copy machines. DO NOT use this probe to measure high voltages on power distribution systems. The probe provides high accuracy when used with a voltmeter having 10 Megohm input impedance.

Ordering information



Fluke 80K 40

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa +31 (0)40 267 5100

In Canada (800)-36-FLUKE

From other countries +1 (425) 446-5500

Fluke Electronics (Malaysia) Sdn Bhd

Suite D-3A-4, Block D

SouthGage Commercial Centre, No2

Jalan Dua Off Jln Chan Sow Lin

55200 KL

Malaysia

Email: info.asean@fluke.com

www.fluke.com/my

©2021 Fluke Corporation. Specifications subject to change without notice.

11/2021

Modification of this document is not permitted without written permission from Fluke Corporation.