

Fluke VPS250 2.5 m Voltage Probe Set 75 MHz



Product overview: Fluke VPS250 2.5 m Voltage Probe Set 75 MHz

Double insulated voltage probe

Specifications: Fluke VPS250 2.5 m Voltage Probe Set 75 MHz

General Specifications	
Attenuation	10x
Bandwidth	75 MHz
Max. input voltage	1000 V
Max. voltage to ground	600 V CAT III, 1000 V CAT II per IEC / EN61010-31
Input resistance	10 Mohm
Input capacitance	18.5 pF
Compensation range	10 to 35 pF
Cable Length	2.5 m
BB120 Shielded Banana to BNC Adapter is required to adapt to ScopeMeter 120 Series shielded banana jack inputs.	

Ordering information



Fluke VPS250

2.5 m Voltage Probe Set 75 MHz

Each probe set includes:

- 600 V CAT III / 1000 V CAT II rated
 - 10:1 Voltage probe
 - Hook clip for probe tip, 4-mm test probe for probe
 - Ground lead with hook clip
 - Ground lead with mini alligator
 - One year warranty
-

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa +31 (0)40 267 5100

In Canada (800)-36-FLUKE

From other countries +1 (425) 446-5500

Fluke Electronics (Malaysia) Sdn Bhd

Suite D-3A-4, Block D

SouthGage Commercial Centre, No2

Jalan Dua Off Jln Chan Sow Lin

55200 KL

Malaysia

Email: info.asean@fluke.com

www.fluke.com/my

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

Modification of this document is not permitted without written permission from Fluke Corporation.