

TECHNICAL DATA

Fluke 700 PMP Pressure Pump



Product overview: Fluke 700 PMP Pressure Pump

Description: The Fluke 700PMP is a hand-operated pressure pump to provide pressures up to 150 psi/1000 kPa. Output fitting is 1/8 FNPT.

Application: Linear stroke of 4 cm. Multi-turn vernier for fine adjustment of pressure.

Specifications: Fluke 700 PMP Pressure Pump

Mechanical and General Specifications	
Size	265 x 35 mm
Weight	340 g
Warranty	One year

Ordering information



Fluke 700PMP

PMP Pressure Pump

Instruction sheet

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

Fluke Electronics (Malaysia) Sdn Bhd

Suite D-3A-4, Block D
SouthGage Commercial Centre, No2
Jalan Dua Off Jln Chan Sow Lin
55200 KL
Malaysia

Email: info.asean@fluke.com

www.fluke.com/my

©2021 Fluke Corporation. Specifications subject to
change without notice.
12/2021

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa +31 (0)40 267 5100

In Canada (800)-36-FLUKE

From other countries +1 (425) 446-5500

**Modification of this document is not permitted
without written permission from Fluke Corporation.**