

TECHNICAL DATA

Fluke TL26A 60 in. 5-Way Test Lead Set



Product overview: Fluke TL26A 60 in. 5-Way Test Lead Set

5 ways to connect:

1. U-shaped nose for blade-shaped terminals
2. Notched jaw for gripping screw heads, bare wire or terminals
3. Serrated teeth for gripping threaded or wire-wrapped terminals
4. Cluster of sharp needles for piercing small gauge (#22-#28 AWG) wires
5. Large piercing needle for penetrating larger gauge wires

Ordering information



Fluke TL26A

60" (1.5m), silicone-insulated leads, useable from -80 °C to +70 °C (-112 °F to +158 °F). Rated for 30V, 8A. One red, one black.

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa +31 (0)40 267 5100

In Canada (800)-36-FLUKE

From other countries +1 (425) 446-5500

Fluke Electronics (Malaysia) Sdn Bhd

Suite D-3A-4, Block D

SouthGage Commercial Centre, No2

Jalan Dua Off Jln Chan Sow Lin

55200 KL

Malaysia

Email: info.asean@fluke.com

www.fluke.com/my

©2021 Fluke Corporation. Specifications subject to change without notice.

11/2021

Modification of this document is not permitted without written permission from Fluke Corporation.