

Fluke TL28A Automotive Test Lead Set



Key features

- Flexible silicone insulated leads are heat and cold resistant
- Cat I 30 V, 10 A

Product overview: Fluke TL28A Automotive Test Lead Set

Large jaws, long leads and a piercing needle inside the jaws. Solid, spring-loaded copper clips with a wide 12.7 mm (.50") jaw opening and serrated teeth. Large piercing needle for penetrating larger gauge wires located inside the jaws. 1.5 m (60"), silicone-insulated leads, useable from -80 °C to +70 °C (-112 °F to +158 °F). Rated for 30 V, 10 A. One red, one black.

Ordering information



Fluke TL28A

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa +31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500

Fluke Electronics (Malaysia) Sdn Bhd
Suite D-3A-4, Block D
SouthGage Commercial Centre, No2
Jalan Dua Off Jln Chan Sow Lin
55200 KL
Malaysia
Email: info.asean@fluke.com
www.fluke.com/my

©2021 Fluke Corporation. Specifications subject to
change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**