

TECHNICAL DATA

Fluke HC120 Hook Clips (Set of 2: Red, Gray)



Product overview: Fluke HC120 Hook Clips (Set of 2: Red, Gray)

Set of two (one red, one gray) Hook Clips, designed for use with STL 120 Shielded Test Leads, VPS40 and TL75 Test Leads. Accepts wires up to 2.5 mm. The contact material is made of reinforced nickel plated steel

Specifications: Fluke HC120 Hook Clips (Set of 2: Red, Gray)

General Specifications	
Maximum voltage	600 V rms. CAT III per IEC 1010-2-031
Maximum wire size	2.5 mm
Contact material	Nickel plated steel

Ordering information



Fluke HC120

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa +31 (0)40 267 5100

In Canada (800)-36-FLUKE

From other countries +1 (425) 446-5500

Fluke Electronics (Malaysia) Sdn Bhd

Suite D-3A-4, Block D

SouthGage Commercial Centre, No2

Jalan Dua Off Jln Chan Sow Lin

55200 KL

Malaysia

Email: info.asean@fluke.com

www.fluke.com/my

©2021 Fluke Corporation. Specifications subject to change without notice.

11/2021

Modification of this document is not permitted without written permission from Fluke Corporation.