

TECHNICAL DATA

Fluke TP82 Insulation Piercing Clip Set



Key features

- Banana jack accepts all DMM and banana jack leads
- Non-rotating banana jack prevents leads from tangling, allowing you to tighten/loosen clamp while still connected to the test lead
- For use with test leads with 2 mm probes
- Tested to 60 V DC

Product overview: Fluke TP82 Insulation Piercing Clip Set

Stainless steel probe pierces insulation on 14, 16 and 18 gauge wire. You control needle depth to minimize insulation damage. Essential for use under hood or under dash. Use it on fuel injectors or sensors while providing complete insulation to grounding due to design.

Ordering information



Fluke TP82

Fluke TP82 Insulation Piercing Clip Set

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa +31 (0)40 267 5100

In Canada (800)-36-FLUKE

From other countries +1 (425) 446-5500

Fluke Electronics (Malaysia) Sdn Bhd

Suite D-3A-4, Block D

SouthGage Commercial Centre, No2

Jalan Dua Off Jln Chan Sow Lin

55200 KL

Malaysia

Email: info.asean@fluke.com

www.fluke.com/my

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

Modification of this document is not permitted without written permission from Fluke Corporation.