

TECHNICAL DATA

Fluke 8.5 MM Scope with 1 M UV Videoscope Probe



Key features

Optional 1 meter long, 8.5 millimeter Ultraviolet videoscope probe with forward view camera. Compatible with Fluke DS701 and Fluke DS703 FC Videoscopes. Supports all features of the Fluke Videoscopes except Up is Up™

Product overview: Fluke 8.5 MM Scope with 1 M UV Videoscope Probe

Ideal for:

Transportation

- Leaks with smoke and dye
- Structural damage of engine components
- Foreign object debris (FOD) inspection

Oil and Gas

- Wear on pipes and hoses
- Structural damage in pipes and hoses

Energy

- Quality control inspections
- Leak inspections

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa +31 (0)40 267 5100

In Canada (800)-36-FLUKE

From other countries +1 (425) 446-5500

Fluke Electronics (Malaysia) Sdn Bhd

Suite D-3A-4, Block D

SouthGage Commercial Centre, No2

Jalan Dua Off Jln Chan Sow Lin

55200 KL

Malaysia

Email: info.asean@fluke.com

www.fluke.com/my

©2021 Fluke Corporation. Specifications subject to change without notice.

11/2021

Modification of this document is not permitted without written permission from Fluke Corporation.