

Wide Angle Infrared Lens RSE



Product overview: Wide Angle Infrared Lens RSE

When working in a tight space, get a wide field of view that lets you see a larger target from a close distance. See an entire bank of switchgear cabinets in tight quarters, or see more components through an IR window. View the entire side of a building without getting too far away, or inspect roofs quicker than with a standard lens by viewing a much larger area at a time.

Avoid the hassle of sending in your camera to calibrate with the lens – with smart lenses you can just attach the lens to any compatible camera and start taking images.

Made of 100% diamond-turned germanium with an engineered coating, the most efficient available material to transmit energy to the detector.

Compatible with RSE300, RSE600.

Specifications: Wide Angle Infrared Lens RSE

Description		
IFOV (spatial resolution)	RSE600	0.93 mRad
	RSE300	1.85 mRad
Field of view	46 ° H x 34 ° V	
Focus distance	15 cm (approximately 6 in)	

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa +31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500

Fluke Electronics (Malaysia) Sdn Bhd
Suite D-3A-4, Block D
SouthGage Commercial Centre, No2
Jalan Dua Off Jln Chan Sow Lin
55200 KL
Malaysia
Email: info.asean@fluke.com
www.fluke.com/my

©2021 Fluke Corporation. Specifications subject to
change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**