

Fluke Networks CIQ-FTKSFP Copper & Fiber Cable Tester Kit



Key features

- Troubleshoots copper cabling and qualifies for 10/100/Gig Ethernet
- SimpliFiber® Pro meter measures power & loss in fiber networks
- Supports multimode 850 and 1300 nm wavelengths
- Quickly verifies network drops: link & ping functionality
- Graphically maps wiring configuration and shows distance to fault

Product overview: Fluke Networks CIQ-FTKSFP Copper & Fiber Cable Tester Kit

The Copper and Fiber Technician's Kit is designed for the IT professional that works with both Copper and Fiber Networks. It offers all of the advantages of the CableIQ™ Kit but it also provides a way to test and verify your fiber connections with the SimpliFiber® Pro Power Meter and Light Source.

Specifications: Fluke Networks CIQ-FTKSFP Copper & Fiber Cable Tester Kit

Cable types supported	UTP, STP, FTP, SSTP, RG6, RG59, audio and security
Qualification autotests	1000BASE-T, 100BASE-TX, 10BASE-T, VoIP, 1394b S100, TELCO, Wiremap only, Coax
Supported tests	Wiremap, length, cable signal performance, digital toner, analog toner, Ethernet port detection and identification, analog telephone detection, blink port light, continuity, speaker test, cable fault finding, video signal detection.
Wiremap	Can detect single wire faults and supports MultiMap mode with up to seven remote office identifiers. Draws proportional wire length to breaks. Detects split pairs.
Find fault	Measures crosstalk and impedance and compares against appropriate limits based on qualification test selected. Detects location of large point sources as well as distributed sources in the cabling if they are sufficient to disqualify the application
Results storage	Up to 250 qualification test results
Power	Battery type: 4 AA (NEDA 15A, IEC LR6) alkaline batteries
Battery life	20 hours of typical use, without backlight
Other battery types supported	4AA photo lithium, NIHM, NICAD
Dimensions and weight	7in x 3.5in x 1.75in (17.8cm x 8.9cm x 4.5cm) 1.2 lb (0.55 kg)

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa +31 (0)40 267 5100

In Canada (800)-36-FLUKE

From other countries +1 (425) 446-5500

Fluke Electronics (Malaysia) Sdn Bhd

Suite D-3A-4, Block D

SouthGage Commercial Centre, No2

Jalan Dua Off Jln Chan Sow Lin

55200 KL

Malaysia

Email: info.asean@fluke.com

www.fluke.com/my

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

Modification of this document is not permitted without written permission from Fluke Corporation.