

Fluke Networks Pro3000™ Probe



Key features

- Loud speaker makes the tone easy to hear through enclosures
- Easy-to-use adjustable volume control dial
- "Quick-twist" tip for easy replacement
- Replacement probe tip stores in battery compartment
- Recessed on/off button

Product overview: Fluke Networks Pro3000™ Probe

The Pro3000™ unfiltered probe, for use on inactive networks, features a loud speaker to hear tone clearly through walls, enclosures and in loud environments. The recessed on/off button helps prevent the probe from accidentally being turned on when stored.

Specifications: Fluke Networks Pro3000™ Probe

User interface	ON/OFF push button Volume dial Replaceable tip 3.5 mm earphone jack
Battery	9V alkaline
Temperature	Operating: -20° C to 60° C, Storage: -40° C to 70° C



Case dimensions	9.8 in. x 1.6 in. x 1.3 in. (24.9 cm x 4.1 cm x 3.3 cm)
-----------------	---

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa +31 (0)40 267 5100

In Canada (800)-36-FLUKE

From other countries +1 (425) 446-5500

Fluke Electronics (Malaysia) Sdn Bhd

Suite D-3A-4, Block D

SouthGage Commercial Centre, No2

Jalan Dua Off Jln Chan Sow Lin

55200 KL

Malaysia

Email: info.asean@fluke.com

www.fluke.com/my

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

Modification of this document is not permitted without written permission from Fluke Corporation.