

TECHNICAL DATA

Fluke C700 Hard Carrying Case



Key features

- **Application:** Cutouts to hold one documenting process calibrator, one Fluke Pressure Module, one BC7210 Battery Charger, one spare BP7217 Battery Pack, and test leads
- **Material:**
 - Exterior: Blow-molded charcoal gray polyethylene with textured surface
 - Interior: Black, die-cut polyurethane foam
- **Handle:** Molded polyethylene
- **Latches:** Zinc-plated steel
- **Dimensions:** 47 x 40 x 14 cm
- **Weight:** 900 g
- **One year warranty**

Product overview: Fluke C700 Hard Carrying Case

Hard carrying case with custom-cut foam liner

Ordering information

**Fluke C700**

Fluke C700 Hard Carrying Case

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2021 Fluke Corporation.
Specifications subject to change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**