


TECHNICAL DATA


## Fluke 3000A/6000A 36-Inch Flexi Probe 4 Phase



### Product overview: Fluke 3000A/6000A 36-Inch Flexi Probe 4 Phase

The 3000/6000A-TF-4 Thin Flex AC Current Probe sets (the Probe or Product) have been designed for applications with Fluke 1735 and Fluke 1740 series products for accurate non-intrusive measurement of ac currents. Using the latest technologies (integrated memory for calibration data) provides current ranges from 0.8 A up to 6000 A in a frequency range of 40 Hz to 5 kHz.

## Ordering information



### **Fluke 3000A/6000A**

36-Inch Flexi Probe 4 Phase

---

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Canada (800) 36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

©2021 Fluke Corporation.  
Specifications subject to change without notice.  
12/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**