

TECHNICAL DATA


Fluke 3210-PR-TF 1000A Flex Thin Flex Current Probe (24 inch/60cm)



Product overview: Fluke 3210-PR-TF 1000A Flex Thin Flex Current Probe (24 inch/60cm)

The Fluke 3210-PR-TF 1000A Flex Thin Flex Current Probe is an ac current probe utilizing the Rogowski principle. The Fluke 3210PRTF Probe is designed for use with the Fluke 1750 Power Recorder and measures current from very low frequencies up to the 50th harmonic of a 50/60 Hz power supply. The flexible and lightweight measuring head allows quick and easy installation in hard to reach areas and around large conductors.

Ordering information



Fluke 3210-PR-TF

1000A Flex Thin Flex Current Probe (24 inch/60cm)

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2021 Fluke Corporation.
Specifications subject to change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**