

Fluke TPS FLEX 24 Flexible Current Probe



Specifications: Fluke TPS FLEX 24 Flexible Current Probe

General Specifications	
Measuring range selectable per software	2 A to 200 A
	10 A to 1000 A
Peak current for sinusoidal currents	480 A
	2700 A
Intrinsic error	1%
Frequency range	45 Hz to 3.0 kHz
Operating voltage	600 V CAT IV
Phase error	0.5°
Jaw opening	61 cm length
	2 m cable
Errors in % of measuring range at 23°C ± 2 K; 74°F ± 2 K, for 48 to 65 Hz Phase angle error at nominal current I _{max} maximum current without time limit (for AC and DC shunts)	

Ordering information



Fluke TPS FLEX 24

Flexible Current Probe



Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2021 Fluke Corporation.
Specifications subject to change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**