

TECHNICAL DATA

Fluke TPS VOLTPROBE 100 V**Specifications: Fluke TPS VOLTPROBE 100 V**

Specifications	
Range rms	1 V to 170 V
Vnom	100 V
Vmax. contin.	1000 V
Fast transient range Vp < 1 ms	6000
Intrinsic error	0.15%
Operating voltage	600 V CAT IV



Ordering information

Fluke TPS

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2022 Fluke Corporation.
Specifications subject to change without notice.
01/2022

**Modification of this document is not permitted
without written permission from Fluke Corporation.**