

TECHNICAL DATA

Fluke TPS VOLTPROBE 10 V**Specifications: Fluke TPS VOLTPROBE 10 V**

Specifications	
Range rms	0.1 V to 17 V
Vnom	10 V
Vmax.contin.	100 V
Fast transient range $V_p < 1$ m	-
Intrinsic error	0.15%
Operating voltage	150 V CAT IV



Ordering information

Fluke TPS

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2022 Fluke Corporation.
Specifications subject to change without notice.
01/2022

**Modification of this document is not permitted
without written permission from Fluke Corporation.**