

TECHNICAL DATA

Fluke TPS VOLTPROBE 1 KV

Specifications: Fluke TPS VOLTPROBE 1 KV

Specifications	
Range rms	10 V to 1700 V
Vnom	2000 V
Vmax. contin.	2000 V
Fast Transient Range Vp < 1 ms	6000
Intrinsic error	> 0.1%
Operating voltage	600 V CAT IV

Ordering information

TPS VOLTPROBE 1KV

Fluke TPS VOLTPROBE 1 KV



Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2022 Fluke Corporation.
Specifications subject to change without notice.
01/2022

**Modification of this document is not permitted
without written permission from Fluke Corporation.**