

TECHNICAL DATA

Fluke 17XX-TL 1.5M Test Lead Set



Product overview: Fluke 17XX-TL 1.5M Test Lead Set

1.5 m test lead for connecting measurement input to Fluke 17XX Power or Energy Loggers.

Ordering information



FLUKE-17XX-TL 1.5M

Test Lead Set, 1000V CAT III, Non-stackable connectors; 1.5M; Red/Blk



Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2021 Fluke Corporation.
Specifications subject to change without notice.
11/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**