

TECHNICAL DATA

## Fluke HC120 Hook Clips (Set of 2: Red, Gray)



### Product overview: Fluke HC120 Hook Clips (Set of 2: Red, Gray)

Set of two (one red, one gray) Hook Clips, designed for use with STL 120 Shielded Test Leads, VPS40 and TL75 Test Leads. Accepts wires up to 2.5 mm. The contact material is made of reinforced nickel plated steel

### Specifications: Fluke HC120 Hook Clips (Set of 2: Red, Gray)

General Specifications	
Maximum voltage	600 V rms. CAT III per IEC 1010-2-031
Maximum wire size	2.5 mm
Contact material	Nickel plated steel

## Ordering information



**Fluke HC120**

---

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Canada (800) 36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

©2021 Fluke Corporation.  
Specifications subject to change without notice.  
11/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**