

TECHNICAL DATA

Fluke 3.8 MM Scope with 1 M Videoscope Probe



Key features

Optional 1 meter long, 3.8 millimeter videoscope probe with forward view camera. Compatible with Fluke DS701 and Fluke DS703 FC Videoscopes. Supports all features of the Fluke Videoscopes except Up is Up™

Product overview: Fluke 3.8 MM Scope with 1 M Videoscope Probe

Ideal for:

Transportation

- Leaks with smoke and dye
- Structural damage of engine components
- Foreign object debris (FOD) inspection

Oil and Gas

- Wear on pipes and hoses
- Structural damage in pipes and hoses

Energy

- Quality control inspections
- Leak inspections

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2021 Fluke Corporation.
Specifications subject to change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**