

## TECHNICAL DATA

# Fluke 5.5 MM Scope with 1 M Videoscope Probe

## Key features

Optional 1 meter long, 5.5 millimeter videoscope probe with dual view camera. Compatible with Fluke DS701 and Fluke DS703 FC Videoscopes. Supports all features of the Fluke Videoscopes except Up is Up™

## Product overview: Fluke 5.5 MM Scope with 1 M Videoscope Probe

Ideal for:

### Industrial

- Some diesel engine inspections
- Combustion chamber inspections
- Inspect welds Inspect computer connections and servers

### Transportation

- Inspection of pumps and hoses
- Inspect welding
- Inspect wiring

### Manufacturing

- Machinery inspection of belts, gears and hoses
- Quality control inspections
- Casting inspections
- Inspect computer connections and servers

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Canada (800) 36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

©2021 Fluke Corporation.  
Specifications subject to change without notice.  
12/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**