

TECHNICAL DATA

Fluke FOM Fiber Optic Meter



Product overview: Fluke FOM Fiber Optic Meter

The Fluke Fiber Optic Meter (FOM) helps you test and maintain fiber optic cable without having to buy a whole new meter. Plug the FOM directly into any DMM with a mV dc function and a 10 M Ω input impedance and quickly and accurately verify fiber optic cable system loss. Light sources and patch cords sold separately.

Ordering information



Fluke FOM

Fluke FOM Fiber Optic Meter

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2021 Fluke Corporation.
Specifications subject to change without notice.
11/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**