

**TECHNICAL DATA**

# Fluke EI-162BN 320 mm Diameter Split Core Transformer



## Key features

External dimensions (LxWxD): 46 x 36 x 16 cm (20.5 x 16 x 17.2 in)

Weight: 8 kg (17.6 lbs)

## Product overview: Fluke EI-162BN 320 mm Diameter Split Core Transformer

Used as a Selective clamp for ground loop resistance measurement around power pylons. Inner diameter of the clamp is 320 mm (12.6 in). Includes the split core transformer. This Split Core Transformer can be used in conjunction with the 1625 Kit or the 1623 Kit.

If non-kit version is owned, the GEOX Probe Cable must be purchased separately.

## Ordering information



### **Fluke EI 162BN**

320 mm Diameter Split Core Transformer

---

Fluke. *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Canada (800) 36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

©2024 Fluke Corporation.  
Specifications subject to change without notice.  
04/2024

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**