

TECHNICAL DATA

## Fluke i1730-flex1500/3pk iFlex® Current Clamps



### Product overview: Fluke i1730-flex1500/3pk iFlex® Current Clamps

The Fluke 1730 Energy Logger 12 inch iFlex® flexible current probes expand the measurement range of the Fluke 1730 to 1500 A ac while providing the ultimate measurement flexibility. The iFlex® probes connect directly to the energy logger, displaying current measurements without error prone scaling factors. The 1.8 m (6 ft) cord allows separation between the measurement location and the energy logger making it easier to view the display. Fluke 1730 Energy Logger iFlex® cables are available in 12, 24, and 36 inch.

## Ordering information



### **Fluke i1730-flex1500/3pk**

1500A 12 inch, 3 Pack

- 
- 1500A 12 inch, 3 pack iFlex® Current Clamps
-

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Canada (800) 36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

©2021 Fluke Corporation.  
Specifications subject to change without notice.  
12/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**