

TECHNICAL DATA

# Fluke L206 Deluxe LED Hat Light



## Key features

- 3 super bright white LEDs
- 360 ° Rotating clip
- 40-hour battery life
- Water resistant
- Durable polymer construction
- Rubber shielded Bezel

## Product overview: Fluke L206 Deluxe LED Hat Light

Attach it to a hard hat, a baseball hat, or even a panel door for all the light you need

## Ordering information



---

### Fluke L206

- Special hard-hat attachment included!
  - Also includes a neck lanyard
  - Hats not included with Deluxe LED Hat Light L206
-

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Canada (800) 36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

©2021 Fluke Corporation.  
Specifications subject to change without notice.  
12/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**