

TECHNICAL DATA

Fluke 80T-150UA Universal Temperature Probe



Key features

- Compatible with Fluke DMMs
- High accuracy and fast reading for low voltage (below 24 V AC, 60 V DC) applications
- Measurement range: -50 to 150 °C
- Output: 1 mV/ °C or 1 mV/ °F (switchable)
- One year warranty

Ordering information



Fluke 80T 150UA

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2021 Fluke Corporation.
Specifications subject to change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**