

## TECHNICAL DATA

**Fluke TPS VOLTPROBE 750 V****Specifications: Fluke TPS VOLTPROBE 750 V**

Specifications	
Range rms	4 V to 680 V
Vnom	400 V
Vmax. contin.	1000 V
Fast Transient Range Vp < 1 ms	5 to 750 detects voltage harmonics > 50st with fast transient
Intrinsic error	0.2%
Operating voltage	600 V CAT IV

## Ordering information

### **TPS VOLTPROBE 750V**

Fluke TPS VOLTPROBE 750 V  
VOLTPROBE 750 V

---

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Canada (800) 36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

©2022 Fluke Corporation.  
Specifications subject to change without notice.  
01/2022

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**