


TECHNICAL DATA

Fluke VPS420-R ScopeMeter® Voltage Probe Set



Ordering information



Fluke VPS420-R

Ruggedized High-Working ScopeMeter Voltage Probe Set

red/black, 100:1, 150 MHz, 1000V CAT III / 600V CAT IV, working voltage (voltage between probe tip and reference lead): 2000V CAT III / 1200V CAT IV.



Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2021 Fluke Corporation.
Specifications subject to change without notice.
11/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**