


TECHNICAL DATA

Fluke 1730-TL0.1M Test Lead Set



Product overview: Fluke 1730-TL0.1M Test Lead Set

100 mm test lead for connecting measurement input to the Fluke 1730 Energy Logger.

Ordering information



Fluke 1730-TL0.1M

1000 V CAT III, straight plug; 0.1 m; silicone; red/black



Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2021 Fluke Corporation.
Specifications subject to change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**