

Fluke Networks CableIQ™ Qualification Tester



Key features

Copper qualification tester troubleshoots and qualifies Ethernet network cabling speed (10/100/1000/VoIP)

- Works on live networks to provide Ethernet switch detection and device configuration
- Measure network capacity (10 Meg, 100 Meg, 1 Gig) to determine support for VoIP, data and video
- Advanced troubleshooting diagnostics; insertion loss, cross talk, noise issues
- Core troubleshooting features; length, distance to fault, graphical wire mapping, opens, shorts, power over Ethernet (POE) detection
- Tests all copper cabling media: twisted-pair, coax, and audio
- Locate and trace cables with digital toning technology. Requires [IntelliTone 200 Digital Probe](#) (included with CIQ-KIT)
- Qualifies and troubleshoots [Industrial Ethernet](#) cabling

Product overview: Fluke Networks CableIQ™ Qualification Tester

CableIQ finds common cable faults and data rate. Cables often fail in harsh industrial environments where cables are exposed to vibration, extreme flexing, moisture, expansion and contraction from temperature change. Failures result in costly production downtime so it's important to quickly identify where the cable is broken so it can be replaced or repaired. CableIQ checks continuity on all wires displays results graphically so you can see opens, shorts, and cross wires and reports the distance to an open connection within the cable. It also checks if the cable can support data rates.

Specifications: Fluke Networks CableIQ™ Qualification Tester

Specifications	
Cable types supported	UTP, STP, FTP, SSTP, RG6, RG59, audio and security
Qualification autotests	1000BASE-T, 100BASE-TX, 10BASE-T, VoIP, 1394b S100, TELCO, Wiremap only, Coax
Supported tests	Wiremap, length, cable signal performance, digital toner, analog toner, Ethernet port detection and identification, analog telephone detection, blink port light, continuity, speaker test, cable fault finding, video signal detection.
Wiremap	Can detect single wire faults and supports MultiMap mode with up to seven remote office identifiers. Draws proportional wire length to breaks. Detects split pairs.
Find fault	Measures crosstalk and impedance and compares against appropriate limits based on qualification test selected. Detects location of large point sources as well as distributed sources in the cabling if they are sufficient to disqualify the application
Results storage	Up to 250 qualification test results
Power	Battery type: 4 AA (NEDA 15A, IEC LR6) alkaline batteries
Battery life	20 hours of typical use, without backlight
Other battery types supported	4AA photo lithium, NIHM, NICAD
Dimensions and weight	7in x 3.5in x 1.75in (17.8cm x 8.9cm x 4.5cm) 1.2 lb (0.55 kg)

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2021 Fluke Corporation.
Specifications subject to change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**