

TECHNICAL DATA

Fluke 700BCA Bar Code Adapter



Product overview: Fluke 700BCA Bar Code Adapter

Description: Shielded four conductor cable terminated with a 9-socket D-subminiature connector and a 9-pin D-subminiature connector.

Application: Provides interconnection and pin translation between a Fluke 743 Documenting Process Calibrator and a Hewlett Packard HBSW-8200 Bar Code Wand.

Specifications: Fluke 700BCA Bar Code Adapter

Mechanical and General Specifications

Size	Overall length approximately 15 cm
Warranty	One year
Material	Black PVC cable and housings, tin plated shells, gold plated copper contacts

Ordering information



Fluke 700BCA

Bar Code Adapter

-
- Interface cable
 - Calibrator to bar code wand
 - Instruction sheet in English, French, German, Italian, and Spanish.
-

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com/en-th

©2022 Fluke Corporation. Specifications subject to
change without notice.
01/2022

**Modification of this document is not permitted
without written permission from Fluke Corporation.**