

Fluke i40s-EL/3pk Clamp-on Current Transformers



Product overview: Fluke i40s-EL/3pk Clamp-on Current Transformers

The Fluke i40s-EL Current Clamp-on Transformer is used for low current measurement; suitable for making measurements up to 40A, and also measures accurately on 1A and 5A secondary current transformers. The i40s-EL jaw is capable of being clamped on current conductors up to 15mm in diameter.

Ordering information



Fluke i40s-EL/3pk

40A Clamp-on Current Transformer, 3 pack

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com/en-th

©2022 Fluke Corporation. Specifications subject to
change without notice.
01/2022

**Modification of this document is not permitted
without written permission from Fluke Corporation.**