

TECHNICAL DATA

Fluke i5sPQ3, 5 A AC Current Clamps, 3-pack



Key features

- Low level current clamp measures up to 5 A AC
- Compact shape makes transporting and storing convenient; the clamp measures only 116 x 43 x 23 mm (4.6 x 1.7 x .9 in)
- Take accurate readings without breaking the circuit
- CAT III 600 V (For insulated conductors only)

Product overview: Fluke i5sPQ3, 5 A AC Current Clamps, 3-pack

A pack of 3 pieces of the i5s current clamps, specially configured to provide low current accuracy while taking measurements on secondary current transformers. This cost-saving 3-pack is perfect for use with 3-phase tools such as the Fluke 434 or Fluke 435. The compact shape makes transporting and storing convenient. Takes accurate readings without breaking the circuit.

Specifications: Fluke i5sPQ3, 5 A AC Current Clamps, 3-pack

Specifications	
Nominal current range	5 A
Continuous current range	10 mA to 6 A
Maximum non-destructive current	70 A

Lowest measurable current	10 mA	
Basic accuracy		48 Hz to 65 Hz
	10 mA to 1 A	1% + 5 mA
	1 A to 5 A	1%
Useable frequency	40 Hz to 5 kHz	
Output level(s)	400 mV/A	
Input load impedance	> 1 MΩ in parallel with up to 47 pF	
Crest factor	≤ 3, add 0.7% to accuracy	
Safety specifications		
Safety	CAT III 600 V per IEC/EN61010-1, Pollution Degree 2	
Maximum voltage	600 V AC	
Mechanical and General Specifications		
Warranty	1 year	
Maximum conductor diameter	15 mm	
Output cable length	2.5 m	
BNC adapter	Yes	
BNC to banana adapter included	No	

Ordering information



Fluke i5sPQ3

5 A ac Current Clamps, 3-pack

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com/en-th

©2022 Fluke Corporation. Specifications subject to
change without notice.
01/2022

**Modification of this document is not permitted
without written permission from Fluke Corporation.**