

TECHNICAL DATA

# Fluke SCC198 Automotive Troubleshooting Kit for 190 Series ScopeMeter



## Key features

The SCC198 Automotive troubleshooting kit includes:

- C190 Hard-shell Carrying Case for 190-Series ScopeMeter
- SW90W FlukeView ScopeMeter Software package
- OC4USB Serial Interface Cable for connecting the ScopeMeter to a (notebook) PC
- STL90 Shielded Test Leads (1 red & 1 gray) with 2 ground leads
- Four Backprobe pins (1 red, 1 gray, 2 black),
- Four 4 mm Tip adapters (1 red, 1 gray, 2 black),
- AC85A Sets of Alligator Clips (Four pieces, 1 red, 1 gray, 2 black)
- C75 Softcase, for holding and storing all smaller items
- Low pass filter adapters (2 pieces)
- BNC(m) to BNC(f) extension cables (2 pieces)

... plus ample storage space to hold all standard accessories and manuals, included with the ScopeMeter testtool (ScopeMeter testtool not included in SCC198)

## Product overview: Fluke SCC198 Automotive Troubleshooting Kit for

## 190 Series ScopeMeter

Using the ScopeMeter 190 Series in dedicated applications like automotive electronics troubleshooting, often requires special accessories like adapters, connectors and test leads to establish the measurement connection to the circuitry under test. The Fluke SCC198 kit provides a host of accessories that allow you to easily and quickly make measurements on automotive electronic systems, using a 190 Series ScopeMeter.

## Ordering information



### Fluke SCC198

Fluke SCC198 Automotive Troubleshooting kit for 190 Series ScopeMeter  
Automotive Troubleshooting kit for 190 Series ScopeMeter

The SCC198 Automotive troubleshooting kit includes:

- C190 Hard-shell Carrying Case for 190-Series ScopeMeter
- SW90W FlukeView ScopeMeter Software package
- OC4USB Serial Interface Cable for connecting the ScopeMeter to a (notebook) PC
- STL90 Shielded Test Leads (1 red and 1 gray) with 2 ground leads
- Four backprobe pins (1 red, 1 gray, 2 black)
- Four 4 mm tip adapters (1 red, 1 gray, 2 black)
- AC85A Sets of alligator clips (Four pieces, 1 red, 1 gray, 2 black)
- C75 Softcase, for holding and storing all smaller items
- Low pass filter adapters (2 pieces)
- BNC(m) to BNC(f) extension cables (2 pieces)

Plus ample storage space to hold all standard accessories and manuals, included with the ScopeMeter test tool (ScopeMeter test tool not included in SCC198)

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Europe/M-East/Africa  
+31 (0)40 267 5100  
In Canada (800)-36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com/en-th](http://www.fluke.com/en-th)

©2022 Fluke Corporation. Specifications subject to  
change without notice.  
01/2022

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**