

**TECHNICAL DATA**

# Fluke L207 High Intensity Light with Collector's Cap



## Key features

- Cap adjusts for all-day comfort
- Light attaches to bill of baseball cap
- Rugged light withstands 6' drops to concrete
- Waterproof light case won't crack or chip
- Electrically and thermally nonconductive

## Product overview: Fluke L207 High Intensity Light with Collector's Cap

Powerful, lightweight, mini-Xenon worklight shines right where you're working. Comes with limited edition Fluke collector's cap.

## Ordering information



### **Fluke L207**

Fluke L207 High Intensity Light with Collector's Cap

---

**Fluke.** *Keeping your world up and running.*®

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Europe/M-East/Africa  
+31 (0)40 267 5100  
In Canada (800)-36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com/en-th](http://www.fluke.com/en-th)

©2022 Fluke Corporation. Specifications subject to  
change without notice.  
01/2022

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**