

## TECHNICAL DATA

# Fluke 80K-6 High Voltage Probe




## Key features

- A high voltage probe that allows a multimeter to measure up to 6,000V. Intended for low energy applications only
- One year warranty

## Product overview: Fluke 80K-6 High Voltage Probe

The 80K-6 is a high voltage probe designed to extend the voltage measuring capability of an AC/DC voltmeter to 6000 volts peak AC or DC Overvoltage Category I. This means the probe can only be used to make measurements on energy limited circuits within equipment. Examples include high voltage within televisions or photo copy machines. DO NOT use this probe to measure high voltages on power distribution systems. The probe provides high accuracy when used with a voltmeter having 10 Megohm input impedance.

## Ordering information



### **Fluke 80K 6**

Fluke 80K-6 High Voltage Probe

---

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Europe/M-East/Africa  
+31 (0)40 267 5100  
In Canada (800)-36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com/en-th](http://www.fluke.com/en-th)

©2022 Fluke Corporation. Specifications subject to  
change without notice.  
01/2022

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**