


TECHNICAL DATA

# Fluke STL120-III Shielded Test Leads Set



## Product overview: Fluke STL120-III Shielded Test Leads Set

**Set of two (one red, one gray) double insulated silicone shielded test leads for noise free measurements.**

Specially designed for use with the Fluke ScopeMeter 120 Series. Compatible with AC120 Alligator Clips and HC120 Hook Clips. Safety designed ground leads included. Integral strain relieve and extra hard probe tips provide extra long service life. Features safety designed shrouded plugs and notched tip to prevent probe from sliding.

## Specifications: Fluke STL120-III Shielded Test Leads Set

| Specifications            |  |
|---------------------------|--|
| Bandwidth                 | 12,5 MHz                                 |
| Maximum signal voltage    | 600 V rms CAT III per IEC 61010-031:2008 |
| Maximum voltage to ground | 600 V rms CAT III per IEC 61010-031:2008 |
| Maximum vcurrent          | 1 A                                      |
| 2 mm add-on testpin       | 600 V CAT II per IEC 61010-031:2008      |
| Length                    | 1.2 m (48)                               |

## Ordering information



### **Fluke STL120 III**

Shielded Test Leads Set

---

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Europe/M-East/Africa  
+31 (0)40 267 5100  
In Canada (800)-36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com/en-th](http://www.fluke.com/en-th)

©2022 Fluke Corporation. Specifications subject to  
change without notice.  
01/2022

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**