

# Fluke TL82 Automotive Pin and Socket Adapter Set



## Product overview: Fluke TL82 Automotive Pin and Socket Adapter Set

An absolute must-have for work on Asian or European vehicles. This collection of male and female adapters allows you to make firm connection to pin and socket connectors. Useful when making voltage, frequency, duty cycle or resistance measurements and a must when measuring current requiring the meter be placed in series in the circuit.

## Ordering information



### Fluke TL82

Fluke TL82 Automotive Pin & Socket Adapter Set  
Automotive Pin & Socket Adapter Set

Set contains:

- Retractable shrouded test leads complete set of 8 pin-and-socket adapters with flexible tips; one red and one black in the following sizes:
  - Size 22 contact 0.030 in. (0.76 mm) rated 3 A
  - Size 20 contact 0.040 in. (1.02 mm) rated 3 A
  - Size 16 contact 0.063 in. (1.60 mm) rated 3 A
  - Size 12 contact 0.093 in. (2.36 mm) rated 3 A
- Tested to 60 V DC

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Europe/M-East/Africa  
+31 (0)40 267 5100  
In Canada (800)-36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com/en-th](http://www.fluke.com/en-th)

©2022 Fluke Corporation. Specifications subject to  
change without notice.  
01/2022

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**