

## TECHNICAL DATA

# Fluke TP82 Insulation Piercing Clip Set



## Key features

- Banana jack accepts all DMM and banana jack leads
- Non-rotating banana jack prevents leads from tangling, allowing you to tighten/loosen clamp while still connected to the test lead
- For use with test leads with 2 mm probes
- Tested to 60 V DC

## Product overview: Fluke TP82 Insulation Piercing Clip Set

Stainless steel probe pierces insulation on 14, 16 and 18 gauge wire. You control needle depth to minimize insulation damage. Essential for use under hood or under dash. Use it on fuel injectors or sensors while providing complete insulation to grounding due to design.

## Ordering information



### **Fluke TP82**

Fluke TP82 Insulation Piercing Clip Set

---

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Europe/M-East/Africa  
+31 (0)40 267 5100  
In Canada (800)-36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com/en-th](http://www.fluke.com/en-th)

©2022 Fluke Corporation. Specifications subject to  
change without notice.  
01/2022

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**