

TECHNICAL DATA

Fluke TP88 Rigid Back Probe Pins



Key features

- Slides onto test probes measuring 2 mm (0.08 inches)
- Tested to 60 V DC

Product overview: Fluke TP88 Rigid Back Probe Pins

Better than a test probe alone – these two inch long rigid back probe pins easily pass between the weather pack seal and wire. A sharp point ensures good contact to the electrical connector, and the pin's insulation protects it from shorting to other wires.

Ordering information



Fluke TP88

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com/en-th

©2022 Fluke Corporation. Specifications subject to
change without notice.
01/2022

**Modification of this document is not permitted
without written permission from Fluke Corporation.**