


TECHNICAL DATA

Fluke 8.5 MM Scope with 3 M Videoscope Probe



Key features

Optional 3 meter long, 8.5 millimeter videoscope probe with dual view camera. Compatible with Fluke DS701 and Fluke DS703 FC Videoscopes. Supports all features of the Fluke Videoscopes except Up is Up™

Product overview: Fluke 8.5 MM Scope with 3 M Videoscope Probe

Ideal for:

Light Industrial

- Quality control testing
- Machinery maintenance inspections
- Inspect switches and gears
- Elevator inspections
- Inspect welds

Heavy Duty Equipment

- Inspect hydraulic lines
- Inspect welds

Energy

- Electrical, inspecting runs

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com/en-th

©2022 Fluke Corporation. Specifications subject to
change without notice.
01/2022

**Modification of this document is not permitted
without written permission from Fluke Corporation.**